

PROXIMAL FEMUR NAIL (A2 Advance)




180mm PFNA Nail

240mm PFNA Nail

OD (mm)	Length (mm)	SS316L	Titanium	OD (mm)	Length (mm)	SS316L	Titanium
9	180	NS.90.09	TNS.90.09	9	240	NS.92.09	TNS.92.09
10	180	NS.90.10	TNS.90.10	10	240	NS.92.10	TNS.92.10
11	180	NS.90.11	TNS.90.11	11	240	NS.92.11	TNS.92.11
12	180	NS.90.12	TNS.90.12	12	240	NS.92.12	TNS.92.12
13	180	NS.90.13	TNS.90.13	13	240	NS.92.13	TNS.92.13

GAMMA3 HIP SCREW



SIZE (mm)	SS316L	Titanium
60	BS.39.60	TBS.39.60
65	BS.39.65	TBS.39.65
70	BS.39.70	TBS.39.70
75	BS.39.75	TBS.39.75
80	BS.39.80	TBS.39.80
85	BS.39.85	TBS.39.85
90	BS.39.90	TBS.39.90
95	BS.39.95	TBS.39.95
100	BS.39.100	TBS.39.100
105	BS.39.105	TBS.39.105
110	BS.39.110	TBS.39.110

OD (mm)	Length (mm)	SS316L	Titanium
Left			
9	340 To 440	NS.94.34 To NS.94.44	TNS.94.34 To TNS.94.44
10	340 To 440	NS.95.30 To NS.95.44	TNS.95.30 To TNS.95.44
11	340 To 440	NS.96.30 To NS.96.44	TNS.96.30 To TNS.96.44
12	340 To 440	NS.97.30 To NS.97.44	TNS.97.30 To TNS.97.44
(20mm Variation in sizes)			

OD (mm)	Length (mm)	SS316L	Titanium
Right			
9	340 To 440	NS.98.34 To NS.98.44	TNS.98.34 To TNS.98.44
10	340 To 440	NS.99.34 To NS.99.44	TNS.99.34 To TNS.99.44
11	340 To 440	NS.100.34 To NS.100.44	TNS.100.34 To TNS.100.44
12	340 To 440	NS.101.34 To NS.101.44	TNS.101.34 To TNS.101.44
(20mm Variation in sizes)			

- PFNA Blade

SIZE (mm)	SS316L	Titanium	SIZE (mm)	SS316L	Titanium
60	BS.39.60	TBS.39.60	100	BS.39.100	TBS.39.100
65	BS.39.65	TBS.39.65	105	BS.39.105	TBS.39.105
70	BS.39.70	TBS.39.70	110	BS.39.110	TBS.39.110
75	BS.39.75	TBS.39.75	115	BS.39.115	TBS.39.115
80	BS.39.80	TBS.39.80	120	BS.39.120	TBS.39.120
85	BS.39.85	TBS.39.85	125	BS.39.125	TBS.39.125
90	BS.39.90	TBS.39.90	130	BS.39.130	TBS.39.130
95	BS.39.95	TBS.39.95			

